



Connectors > Power Connectors > Circular Power > Circular Power Connectors



Number of Positions: 37

Connector Product Type: **Housing**

Operating Voltage: 600 VDC

Connector System: **Wire-to-Wire**

Sealable: **No**

Features

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Plug
Circular Connector Shell Type	All Plastic

Configuration Features

Reverse Numbering	Without
Number of Positions	37
Number of Power Positions	0
Number of Signal Positions	37

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features



Reverse Gender	Yes
Contact Type	Pin
Contact Protection	With

Mechanical Attachment

Mating Retention Type	Threaded Coupling
Thread Size	1-3/8 - 18 UNEF-2A
Polarization Code	A
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)
Mating Retention	With
Panel Mount Feature	Without

Housing Features

Body Orientation	Straight
Housing Color	Black
Housing Material	Nylon 6/6 GF
Circular Connector Shell Size	23

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	None

Operation/Application

Circuit Application	Power & Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 164159-4
M-SRS PIN ASSY 3+



TE Part # 202726-1
CONTACT SOCKET ASSY.



TE Part # 356611-2
DIES POWERBAND CONT 10 AWG
DIE SET



TE Part # 66393-7
III+ PIN,30-26,15AU/FL,STRIP



TE Part # 66332-8
III+ PIN,24-20,30AU/FL,STRIP



TE Part # 66109-4
III+ SKT,26-24,30AU/FL,LP



TE Part # 66181-1
III+ SKT,SOLDER,30AU,10AU FLASH,LP








TE Part # 66109-3
III+ SKT,26-24,15AU/FL,LP



 TE Part # 206306-5 CPC RECEPT ASSEMBLY SIZE 23-37	 TE Part # 213845-5 POWERBAND CONT ASSY,SILVER PLT	 TE Part # 164164-2 PIN ASS	 TE Part # 1-66098-8 III+ PIN,18-16,TIN STRIP
 TE Part # 66405-4 III+ SKT,30-26,30AU/FL,LP	 TE Part # 1-66564-2 III+ PIN,24-20,TIN,STRIP	 TE Part # 66360-3 III+ SKT,18-14,15AU/FL,LP	 TE Part # 1-66105-9 III+ SKT,24-20,TIN,LP
 TE Part # 164160-3 M-SRS PIN ASSY 3+	 TE Part # 3-66104-0 III+ SKT,24-20,TIN ,STRIP	 TE Part # 66108-7 III+ SKT,26-24,15AU/FL,STRIP	 TE Part # 66566-7 III+ PIN,24-20,TIN,LP

Also in the Series

AMP CPC

 Circular Connector Backshells & Clamps(1)	 Circular Power Connectors(211)	 Connector Contacts(260)	 Connector Hardware(12)
 Power Contacts(260)	 Sealing Sleeves(2)		

Also in the Series

CPC Series 1



Circular Power Connectors(211)



Connector Contacts(260)



Power Contacts(260)

Customers Also Bought



TE Part #206306-5
CPC RECEPT ASSEMBLY SIZE 23-37



TE Part #206070-8
CABLE CLAMP KIT #17



TE Part #66102-3
III+ PIN,24-20,15AU/FL,STRIP



TE Part #206151-1
23-37 RECEPT STD SEX



TE Part #206306-2
23-37 F H RECEPT REV SEX




TE Part #206044-1
CPC PLUG ASSEMBLY SIZE 17-14




TE Part #213850-1
CPC PLUG ASSEMBLY SIZE 23-37



TE Part #EC7552-000
HL104WE1TS025B



TE Part #CM6264-000
TTMS-MP-12.7-9



TE Part #2846666-1
GAMMA CS 8POS PLUG ASSY

Documents

Product Drawings

CPC PLUG ASSEMBLY SIZE 23-37

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_206305-1_L.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_206305-1_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_206305-1_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMP Circular Connectors for Commercial Signal & Power Applications](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English