



Part Number : [190220015](#)
Product Description : Krimptite Quick Disconnect, Male, for 10-12 (5.00-3.30mm²) Wire, Box, Tab 6.35 x 0.81mm
Series Number : 19022
Status : Active
Product Category : Quick Disconnects
Engineering Number : CMCT-1



Documents & Resources

Drawings

[190220015_sd.pdf](#)

3D Models and Design Files

[190220015_stp.zip](#)

Specifications


[PS-19902-005-001.pdf](#)

[PS-19902-011-001.pdf](#)

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D

- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19022
Description	Krimptite Quick Disconnect, Male, for 10-12 (5.00-3.30mm ²) Wire, Box, Tab 6.35 x 0.81mm
Comments	Economical
Product Name	Krimptite
Type	Quick Disconnect
UPC	800755050127

Electrical

Voltage - Maximum	Per Wire Specification
-------------------	------------------------

Physical

Barrel Type	Closed
Gender	Male
Glow-Wire Capable	No
Insulated	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Zinc Chromate
Material - Plating Termination	Zinc Chromate
Net Weight	1.270/g

Orientation	Straight
Packaging Type	Bag
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	Per Wire Specification
Wire Size (AWG)	10, 12