



Part Number : [192070001](#)  
Product Description : VersaKrimp Parallel  
Splice for 22-18 AWG Wire  
Series Number : 19207  
Status : Active  
Product Category : Splices  
Engineering Number : AS-302



Documents & Resources

Drawings  
[192070001\\_sd.pdf](#)

Specifications  
[PS-19902-011-001.pdf](#)  
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                          |
| China RoHS         |  |
| EU ELV             | Not Relevant                                                                          |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                        |
| REACH SVHC         | Not Contained per D(2024)6225-DC (07 Nov 2024)                                        |
| EU RoHS            | Compliant per EU 2015/863                                                             |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

|              |                                               |
|--------------|-----------------------------------------------|
| Status       | Active                                        |
| Category     | Splices                                       |
| Series       | 19207                                         |
| Description  | VersaKrimp Parallel Splice for 22-18 AWG Wire |
| Product Name | Parallel,VersaKrimp                           |
| UPC          | 800755061239                                  |

#### Agency

|     |         |
|-----|---------|
| CSA | LR18689 |
| UL  | E32244  |

#### Physical

|                                |                 |
|--------------------------------|-----------------|
| Barrel Type                    | Closed - Brazed |
| Insulation                     | None            |
| Material - Metal               | Copper          |
| Material - Plating Mating      | Tin             |
| Material - Plating Termination | Tin             |
| Net Weight                     | 0.766/g         |
| Packaging Type                 | Bag             |
| Wire Size (AWG)                | 18, 20, 22      |

---

### Application Tooling

#### Global

|             |             |
|-------------|-------------|
| Description | Part Number |
|-------------|-------------|

|                                                                                                                                             |                  |
|---------------------------------------------------------------------------------------------------------------------------------------------|------------------|
| PremiumGrade Hand Crimp Tool<br>for Krimptite/Versakrimp Terminals<br>and Splices, 22-10 AWG and<br>6.0mm <sup>2</sup> - 0.5mm <sup>2</sup> | <u>640030100</u> |
| Crimp Head for the AT-200<br>Pneumatic Hand Tool                                                                                            | <u>640070100</u> |
| ServiceGrade Hand Crimp Tool -<br>Ratchet                                                                                                   | <u>640160038</u> |

---

This document was generated on Mar 06, 2025