

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-2208103-6
2POS,HVA,2 PHM,SHUNTED,HYB ASSY

TE Part # 2343354-1
EV31 OVERSEA ACCM CABLE

TE Part # 4-2208103-4
2POS,HVA,2 PHM,SHUNTED,HYB ASSY

TE Part # 1-2208103-6
2POS,HVA,2 PHM,SHUNTED,HYB ASSY



 TE Part # 4-2208103-5 2POS,HVA,2 PHM,SHUNTED,HYB ASSY	 TE Part # 5-2208103-5 2POS,HVA,2 PHM,SHUNTED,HYB ASSY	 TE Part # 2103534-4 PLUG SUBASSY, D, HVA280	 TE Part # 4-2103015-6 PLUG SUBASSY, F, HVA280-2PHM F
 TE Part # 2103534-1 PLUG SUBASSY, A, HVA280	 TE Part # 2-2208103-2 2POS,HVA,2 PHM,SHUNTED,HYB ASSY	 TE Part # 2350369-2 EV63 PHRASE II ACCM CABLE HARNESS	 TE Part # 4-2208103-0 2POS,HVA,2 PHM,SHUNTED,HYB ASSY
 TE Part # 2103534-6 PLUG SUBASSY, F, HVA280	 TE Part # 4-2103015-1 PLUG SUBASSY, A, HVA280-2PHM F	 TE Part # 1-2208103-5 2POS,HVA,2 PHM,SHUNTED,HYB ASSY	 TE Part # 2103169-5 OUTER HOUSING, CAP, KEY E, HVA280-2PHM
 TE Part # 2343236-1 EV51-B1 OBC CABLE	 TE Part # 1-2208103-2 2POS,HVA,2 PHM,SHUNTED,HYB ASSY	 TE Part # 1-2208103-4 2POS,HVA,2 PHM,SHUNTED,HYB ASSY	 TE Part # 1-2208103-1 2POS,HVA,2 PHM,SHUNTED,HYB ASSY

Customers Also Bought

 TE Part #2141608-4 5POS,AMP MCP6.3/4.8K,REC HSG,A	 TE Part #9-1768016-7 CSL-14033P-9	 TE Part #282021-014 44A0111-20-1	 TE Part #1-2103124-1 HEADER ASSY, Ag SHIELD, KEY A, HVA280-2P
--	---	---	--



Documents

Product Drawings

CABLE SEAL, SIZE 1, HVA280

English

CABLE SEAL, SIZE 1, HVA280

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2103154-1_A_c-2103154-1-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2103154-1_A_c-2103154-1-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2103154-1_A_c-2103154-1-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

English

Application Specification

English



Application Specification

English