


Power Triple Lock

TE Internal #: 5-1971874-7

TE Internal Description: PTL 3X5 CAP FREE HANG HITEMP KEY A

LGR

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Also in the Series | **Power Triple Lock**



Connector Contacts(26)



Connector Hardware(12)



PCB Headers & Receptacles(21)




Power Contacts(26)



Rectangular Connector Housings(280)



Rectangular Power Connectors(301)




Standard Rectangular Connectors(280)

Customers Also Bought




TE Part #EC9833-000
ZHD-SCE-3.2-50-S1-4



TE Part #1614770-4
BDS 2 A 250 10R 10%



TE Part #1-1415543-5
RTE44110



TE Part #55992-1
TERMINAL,AMPOWER R 2/0 5/16



TE Part #ASA158F12390235000
623 PLUG



TE Part #ZPF000000000205373
PLUG MALE ANG.90 CAL.20 - FXP



TE Part #ZPF000000000136485
RECEPTACLE MALE FOR 12 PINS,
CAL1,6



TE Part #YZ-KC-212751A-PY00
TOOL DISMOUNTING - FXP2



TE Part #ZPF000000000205378
CONTACT MALE ANG.90, CAL20,
120MM2 - FXP



TE Part #ZPF000000000205388
CONTACT FEMALE CAL.20, M12 - FXP



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-1971874-7_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-1971874-7_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-1971874-7_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773734-9 TE Power Triple Lock Quick Reference Guide - German

German

9-1773465-1Power Triple Lock QRG

English

Product Specifications

Application Specification

English

Agency Approvals

VDE Certificate

English

VDE Certificate

English