



Part Number : 936010494
Product Description : GWconnect Pneumatic Contact, Female, with Shutoff valve, for 4.00mm I.D. Tubes, Black
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Contacts
Engineering Number : 7700.3558.0



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Heavy-Duty Contacts
Series	93601
Description	GWconnect Pneumatic Contact, Female, with Shutoff valve, for 4.00mm I.D. Tubes, Black
Comments	with Shutoff
Contact Type	Pneumatic
Product Name	GWconnect
UPC	887191823195

Physical

Color - Resin	Black
Gender	Female
Length	23.00mm
Material - Contact	Polypropylene
Net Weight	0.580/g
Packaging Type	Bag

Use with Part(s)

Description	Part Number
Use With	4.00mm Internal Diameter Tubes, up to 8 bar / 116 psi