



Part Number : [936000225](#)
Product Description : GWconnect Ribbon Cable Gland, Size 10B, Waterproof/Dustproof, Ribbon Cable 3.80-9.00mm x 26.00-35.00mm, Grey RAL 7037
Series Number : 93600
Status : Active
Product Category : Heavy-Duty Cable Glands
Engineering Number : 7000.7361.0



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per ED/71/2019 (16 July 2019)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Heavy-Duty Cable Glands
Series	93600
Description	GWconnect Ribbon Cable Gland, Size 10B, Waterproof/Dustproof, Ribbon Cable 3.80-9.00mm x 26.00-35.00mm, Grey RAL 7037
Cable Gland Type	IP66 - Ribbon Cable
IP Rating	IP66
Product Name	GWconnect
UPC	887191843179

Physical

Component Size	10B «57X27»
Gland Color	Grey RAL 7037
Material - Cable Gland	Polyamide
Material - Gasket	Silicone
Net Weight	73.000/g
Packaging Type	Bag
Ribbon Cable Size	3.80-9.00mm X 26.00-35.00m
Temperature Range - Operating	-40° to +100°C
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP66, IP69

Use with Part(s)

Description	Part Number
Use With	Ribbon cables
