



Part Number : 936000392
Product Description : GWconnect Plastic
Gable Gland, with Gasket, Pg9 Thread, Black
RAL 9005
Series Number : 93600
Status : Active
Product Category : Heavy-Duty Cable Glands
Engineering Number : 7000.7830.1



Product Environment Compliance

Compliance

| | |
|--------------------|--|
| GADSL/IMDS | Not Relevant |
| China RoHS | |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2024)6225-DC (07 Nov 2024) |
| EU RoHS | Compliant per EU 2015/863 |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|--------|--------|
| Status | Active |
|--------|--------|

| | |
|------------------|--|
| Category | Heavy-Duty Cable Glands |
| Series | 93600 |
| Description | GWconnect Plastic Gable Gland, with Gasket, Pg9 Thread, Black RAL 9005 |
| Cable Gland Type | IP68 with Gasket |
| IP Rating | IP68 |
| Product Name | GWconnect |
| Standard | DIN 40430, EN 60529 |
| UPC | 887191854946 |

Physical

| | |
|-------------------------------|----------------|
| Cable Diameter | 4.00-8.00mm |
| Gland Color | Black RAL 9005 |
| Material - Cable Gland | Polyamide |
| Material - Gasket | NBR |
| Material - Nut | Polyamide |
| Net Weight | 6.500/g |
| Packaging Type | Bag |
| Panel Cutout Diameter | 15.40mm |
| Panel Mount | Yes |
| Temperature Range - Operating | -40° to +100°C |
| Thread Size | Pg9 |
| Thread Type | (Pg) |
| Waterproof / Dustproof | Yes |
| Waterproof / Dustproof Type | IP68 |

Use with Part(s)

| | |
|-------------|-----------------------------|
| Description | Part Number |
| Use With | Sealed Enclosures and Boxes |