



Part Number : 936000410
Product Description : GWconnect Plastic
Gable Gland, with Gasket, Pg16 Thread, Black
RAL 9005
Series Number : 93600
Status : Active
Product Category : Heavy-Duty Cable Glands
Engineering Number : 7000.7833.1



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Heavy-Duty Cable Glands
Series	93600
Description	GWconnect Plastic Gable Gland, with Gasket, Pg16 Thread, Black RAL 9005
Cable Gland Type	IP68 with Gasket
IP Rating	IP68
Product Name	GWconnect
Standard	DIN 40430, EN 60529
UPC	887191856322

Physical

Cable Diameter	9.00-13.00mm
Gland Color	Black RAL 9005
Material - Cable Gland	Polyamide
Material - Gasket	NBR
Material - Nut	Polyamide
Net Weight	14.000/g
Packaging Type	Bag
Panel Cutout Diameter	22.80mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +100°C
Thread Size	Pg16
Thread Type	(Pg)
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

Use with Part(s)

Description	Part Number
Use With	Sealed Enclosures and Boxes