



[All Signal Header \(246\)](#)

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 172254-2
8P CAP HSG D.L.I. CONN.V


Customers Also Bought




TE Part #2013393-1
ME CONN MOLD TYPE TAB HSG
32POS ASSY R




TE Part #234156-6
CRIMPER WIRE SPECIAL



TE Part #173860-1
070 MULTILOCK CAP ASSY 14P



TE Part #776262-1
14POS,PIN DIA 1.3,HDR ASSY,
180DEG,COD 1



TE Part #5053132039
RNF-100-1/4-9-STK



TE Part #1393304-9
V23134J1052D642-EV-CBOX



TE Part #2237122-2
4POS,TAB0.64X0.64,HDR ASSY,
90DEG,COD 2



TE Part #172258-1
DLI 16POS CAP ASSY V TIN



TE Part #2-1463047-1
ANVIL,GIC 2.5



TE Part #172041-1
MIC CAP 11P W-W

Documents

CAD Files

Customer View Model

[ENG_CVM_172260-1_F1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_172260-1_F1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_172260-1_F1.2d_dxf.zip](#)



English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

Japanese

Instruction Sheets

Customer Manual (non U.S.)

Japanese

Customer Manual (non U.S.)

English

DLI CONNECTORS

English

Customer Manual (non U.S.)

English

DLI CONNECTORS

English