

All AMP MCP, SEALED CONNECTOR HOUSING (130)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM705-T273
AMP MCP, RECEPTACLE AND TAB



TE Part # 964971-1
EINZELLEITERDICHTNG



TE Part # 1718705-1
SINGLE WIRE SEAL,COLLAR DIA 2,



TE Part # 963530-1
EINZELLEITERDICHTNG



TE Part # 1897207-2
MCP 1.5 5P CAP HSG



TE Part # 964972-1
EINZELLEITERDICHTNG



TE Part # 963531-1
BLINDSTOPFEN

Customers Also Bought



TE Part #HDC36-24
DUST CAP, 24SZ, REC, AL, LANYARD, HD30



TE Part #1241380-2
AMP MCP 1.5K, CONTACT, SWS




TE Part #HDP26-18-21SN
PLG, 21P, BLK, N, 20, S



TE Part #HD34-24-91PN-059
REC,9P,AL,N,CBLCLMPBT,DRAIN,8/12 /16,P,MC



TE Part #WHDS-24-2
STRAIN RELIEF, HD30, 24SZ, RA



TE Part #828986-1
DICHT-STOPFEN



TE Part #964269-3
TAB A 1.6x0.6 CONTACT CF SWS Au



TE Part #42098-2
FF 250 TAB 18-14 AWG PTPB



TE Part #DT06-2S-CE13
PLG, 2P, BLK, E, SEAL RET, XCAP



TE Part #1897207-2
MCP 1.5 5P CAP HSG

Documents



Product Drawings

MCP 1.5 5P PLUG ASSY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1897208-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1897208-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1897208-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English