



**Part Number :** [1301460059](#)  
**Product Description :** Watertite Extreme Connector, 2 Pole/3 Wire, NEMA 7-15, 277V, Cord Grip Body Size F2, Silicone Husk  
**Series Number :** 130146  
**Status :** Active  
**Product Category :** Wiring Devices  
**Engineering Number :** 15W34



---

## Documents & Resources

**Drawings**  
[1301460059\\_sd.pdf](#)

**3D Models and Design Files**  
[1301460059\\_stp.zip](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Connector, 2 Pole/3 Wire, NEMA 7-15, 277V, Cord Grip Body Size F2, Silicone Husk
IP Rating	IP69K
NEMA Configuration	NEMA 7-15
Product Name	Watertite Extreme
Specialty	N/A
Type	Connector
UPC	78678871104

### Agency

CSA	LR6837
UL	E10176

### Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	277V

### Physical

Cord Grip Body Size	F2 1/2"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No

Locking Blade	No
Poles	2-pole/3-wire
Receptacle Type	Single