

Part Number : <u>1301460156</u> Product Description : Watertite Extreme Receptacle with Single Flip Coverplate, 2 Pole/2 Wire, NEMA-L2-20, 250V Series Number : 130146 Status : Active Product Category : Wiring Devices Engineering Number : 67W07



Documents & Resources

Drawings 1301460156_sd.pdf

3D Models and Design Files 1301460156_stp.zip

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Receptacle with Single Flip Coverplate, 2 Pole/2 Wire, NEMA-L2-20, 250V
IP Rating	IP67
NEMA Configuration	NEMA L2-20
Product Name	Watertite Extreme
Specialty	N/A
Туре	Receptacle
UPC	78678871458

Agency

CSA	LR6837
UL	E68122

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No

Locking Blade	Yes
Poles	2-pole/2-wire
Receptacle Type	Single

This document was generated on Mar 13, 2025