



Part Number : [1301470058](#)
Product Description : Watertite Extreme Connector for Male Receptacle with Locking Blade, Single Flip Coverplate, 3 Pole/4 Wire, NEMA L15-20, 3ø 250V, F3
Series Number : 130147
Status : Active
Product Category : Wiring Devices
Engineering Number : 27W75MB



Documents & Resources

Drawings
[1301470058_sd.pdf](#)

3D Models and Design Files
[1301470058_stp.zip](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Connector for Male Receptacle with Locking Blade, Single Flip Coverplate, 3 Pole/4 Wire, NEMA L15-20, 3Ø 250V, F3
IP Rating	IP67
NEMA Configuration	NEMA L15-20
Product Name	Watertite Extreme
Specialty	N/A
Type	Connector
UPC	78678871373

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	3Ø 250V

Physical

Cord Grip Body Size	F3 3/4"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes

Poles	3-pole/4-wire
Receptacle Type	Single

This document was generated on Mar 13, 2025