



Part Number : [1301470082](#)
Product Description : Watertite Extreme Extra
Hard Outdoor Plug with Locking Blade, 3
Pole/4 Wire, NEMA L16-30, 3ø 480V, Cord Grip
Body Size F4, Black
Series Number : 130147
Status : Active
Product Category : Wiring Devices
Engineering Number : 28W76BLK



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Extra Hard Outdoor Plug with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3Ø 480V, Cord Grip Body Size F4, Black
IP Rating	IP67
NEMA Configuration	NEMA L16-30
Product Name	Watertite Extreme
Specialty	N/A
Type	Plug
UPC	78678875368

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	3Ø 480V

Physical

Cord Grip Body Size	F4 1"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Male
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Net Weight	0.291/kg
Poles	3-pole/4-wire
Receptacle Type	N/A

This document was generated on Mar 13, 2025