



**Part Number :** [1301470089](#)  
**Product Description :** Watertite Extreme Connector with Locking Blade, 3 Pole/3 Wire, Non-NEMA, 250V, Cord Grip Body Size F4  
**Series Number :** 130147  
**Status :** Active  
**Product Category :** Wiring Devices  
**Engineering Number :** 29W08



---

## Documents & Resources

**Drawings**  
[1301470089\\_sd.pdf](#)

**3D Models and Design Files**  
[1301470089\\_stp.zip](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Connector with Locking Blade, 3 Pole/3 Wire, Non-NEMA, 250V, Cord Grip Body Size F4
IP Rating	IP67
NEMA Configuration	Non-NEMA Locking
Product Name	Watertite Extreme
Specialty	N/A
Type	Connector
UPC	78678871392

### Agency

CSA	LR6837
UL	E10176

### Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	250V

### Physical

Cord Grip Body Size	F4 1"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes

Net Weight	391.903/g
Poles	3-pole/3-wire
Receptacle Type	Single