



**Part Number :** [1301470176](#)  
**Product Description :** Watertite Extreme  
Receptacle with Locking Blade, Single Flip  
Coverplate, 3 Pole/4 Wire, NEMA L17-30, 3ø  
600V  
**Series Number :** 130147  
**Status :** Active  
**Product Category :** Wiring Devices  
**Engineering Number :** 69W77



---

## Documents & Resources

**Drawings**  
[1301470176\\_sd.pdf](#)

**3D Models and Design Files**  
[1301470176\\_stp.zip](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Receptacle with Locking Blade, Single Flip Coverplate, 3 Pole/4 Wire, NEMA L17-30, 3Ø 600V
IP Rating	IP67
NEMA Configuration	NEMA L17-30
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678871582

### Agency

UL	E68122
----	--------

### Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	3Ø 600V

### Physical

Cord Type	N/A
Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Poles	3-pole/4-wire

Receptacle Type	Single
-----------------	--------

---

This document was generated on Mar 13, 2025