



**Part Number :** [1301490040](#)  
**Product Description :** Safeway Flanged  
Receptacle with Locking Blade, 2 Pole/3 Wire,  
NEMA L6-20, 250V  
**Series Number :** 130149  
**Status :** Active  
**Product Category :** Wiring Devices  
**Engineering Number :** 2748MB



---

## Documents & Resources

**Drawings**  
[1301490040\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130149
Description	Safeway Flanged Receptacle with Locking Blade, 2 Pole/3 Wire, NEMA L6-20, 250V
IP Rating	N/A
NEMA Configuration	NEMA L6-20
Product Name	Safeway
Specialty	N/A
Type	Receptacle
UPC	78678870510

### Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	250V

### Physical

Cord Type	N/A
Flange	Yes
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Poles	2-pole/3-wire
Receptacle Type	Single