



Part Number : 1301550154

Product Description : Watertite Extreme Connector with California Style Locking Blade, 2 Pole/3 Wire, Non-NEMA, 250V, Cord Grip Body Size F5

Series Number : 130155

Status : Active

Product Category : Wiring Devices

Engineering Number : CS82W64



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices

Series	130155
Description	Watertite Extreme Connector with California Style Locking Blade, 2 Pole/3 Wire, Non-NEMA, 250V, Cord Grip Body Size F5
IP Rating	IP67
NEMA Configuration	Non-NEMA Locking CA
Product Name	Watertite Extreme
Specialty	N/A
Type	Connector
UPC	78678801460

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	50.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Grip Body Size	F5 1 1/4"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Net Weight	125.644/g
Poles	2-pole/3-wire
Receptacle Type	Single