



Part Number : [1200700082](#)
Product Description : Micro-Change (M12)
PCB Mounting Receptacle, 3 Poles, Female,
90° Angle
Series Number : 120070
Status : Obsolete
Product Category : Circular Industrial
Connectors
Engineering Number : 8R3L510005



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	Circular Industrial Connectors
Series	120070
Description	Micro-Change (M12) PCB Mounting Receptacle, 3 Poles, Female, 90° Angle
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Micro-Change (M12)
Type	PCB Mount
UPC	78678844283

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Coupling Type	Internal Thread
Gender	Female
Keyway	Single
Length	N/A
Material - Component	Nylon
Mounting Thread Size	M12 x 1.0
Net Weight	8.618/g
Orientation	90° Angle
Panel Mount	Front
Poles	3
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	N/A
Wire Size (AWG)	N/A