Specifications



Sealed anti-condensation valves IP68 ØM12 F120 litres/hour when 0,07 bar

Local distributor code: 387530992

NSYCAG12LPH2

EAN Code: 3606480166549

Main

Range	ClimaSys	
Product	ClimaSys CA	
Range compatibility	Thalassa Thalassa PLS Thalassa Thalassa PLM Thalassa Thalassa TBS Thalassa Thalassa TBP	
Product or component type	Pressure release valve	
Accessory / separate part category	Thermal management accessory	
Environmental characteristic	Water resistant	
Fixing mode	Screwed	
Device composition	1 valve	
Quantity per set	Set of 10	

Complementary

Material	Membrane: acrilic co-polymer PA6
Diameter	10.2 mm
Height	30 mm
Width	140 mm
Flame retardance	V2
Operating temperature	-40150 °C
Permeability	120 l/h
Pressure difference	< 0.1 bar

Packing Units

•	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.200 cm
Package 1 Width	2.000 cm
Package 1 Length	2.000 cm
Package 1 Weight	4.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Height	2.500 cm
Package 2 Width	8.000 cm
Package 2 Length	14.000 cm
Package 2 Weight	40.000 g

Logistical informations

Country of origin

TR

Contractual warranty

Warranty

18 months

🜔 Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No	
Packaging without single use plastic	No	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)	

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No