

BFW-M12M4A-6SL

► FIELD WIREABLE CONNECTORS



Field Wireable: M12
4-pin Right Angle Male
22 AWG 4-6 mm Cable Range; Slide Lock Terminal
PA+GF Black Body; Aluminum Alloy Coupling Nut
Part Number: 817096



SPECIFICATIONS

Maximum Temp. (Celsius)	85
Current Rating (A)	4.0
Minimum Temp. (Celsius)	-40
Voltage Rating (V)	250 V ac/dc
Termination	Slide Lock
Connector 1 Orientation	Right Angle
Connector 1 Number of Contacts	4

IP Rating	IP68
Connector 1 Type	M12
Connector 1 Gender	Male
Outside Cable Diameter (mm)	4 to 6.5
Connector 1 Key Code	A