



Part Number : 1301020171

Product Description : Super-Safeway Rubber Hand Lamp with 100W, Open End Guard with Reflector, with Receptacle

Series Number : 130102

Status : Active

Product Category : Lamps and Lights

Engineering Number : 114U



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights

Series	130102
Description	Super-Safeway Rubber Hand Lamp with 100W, Open End Guard with Reflector, with Receptacle
NEMA Configuration	N/A
Product Name	Super-Safeway
Type	Hand Lamps
UPC	78678860480

Agency

CSA	LR85374
UL	E59251

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	240V

Physical

Bulb Type	Incandescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	153.92mm (6.060")
Duty	Industrial
Guard Included	Yes
Guard Type	Open End, Reflector
Height	311.66mm (12.270")
Lamp Type	A21
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Net Weight	439.077/g
Outlet	Side
Packaging Type	Carton

This document was generated on Mar 26, 2025