



Part Number : 1301020229

Product Description : Super-Safeway Rubber  
Hand Lamp, PAR 38 Guard, with Switch

Series Number : 130102

Status : Active

Product Category : Lamps and Lights

Engineering Number : 119S



---

## Product Environment Compliance

### Compliance

|                    |              |
|--------------------|--------------|
| China RoHS         | Not Reviewed |
| EU ELV             | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC         | Not Reviewed |
| EU RoHS            | Not Reviewed |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

|          |                  |
|----------|------------------|
| Status   | Active           |
| Category | Lamps and Lights |

|                    |   |
|--------------------|---|
| Series             | 130102  |
| Description        | Super-Safeway Rubber Hand Lamp, PAR 38 Guard, with Switch |
| NEMA Configuration | N/A   |
| Product Name       | Super-Safeway   |
| Type               | Hand Lamps  |
| UPC                | 78678860200   |

## Agency

|     |         |
|-----|---------|
| CSA | LR85374 |
|-----|---------|

## Electrical

|                             |      |
|-----------------------------|------|
| Lamp Wattage - Maximum      | 100W |
| Lumens                      | 1000 |
| On/Off Switch               | Yes  |
| Voltage (Fixture) - Maximum | 240V |

## Physical

|                         |                            |
|-------------------------|----------------------------|
| Bulb Type               | Incandescent               |
| Cord Length - Primary   | N/A                        |
| Cord Length - Secondary | N/A                        |
| Depth                   | N/A                        |
| Duty                    | Industrial                 |
| Guard Included          | Yes                        |
| Guard Type              | Open End, PAR 38           |
| Height                  | 285.50mm (11.240")         |
| Lamp Type               | PAR38                      |
| Length                  | N/A                        |
| Material - Guard        | #8 Gauge Zinc-plated Steel |
| Mounting Style          | Hand Held                  |
| Outlet                  | None                       |
| Packaging Type          | Carton                     |