



Part Number : 1301050028

Product Description : Super-Safeway Rubber Hand Lamp 75W with LOVOLT In-line Transformer Screw Release Guard, Cord Type 14/2 SOOW, 7.62m (25.0') Cord Length

Series Number : 130105

Status : Active

Product Category : Lamps and Lights

Engineering Number : 1600-12A



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights

Series	130105
Description	Super-Safeway Rubber Hand Lamp 75W with LOVOLT In-line Transformer Screw Release Guard, Cord Type 14/2 SOOW, 7.62m (25.0') Cord Length
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	Hand Lamps, Specialty Light
UPC	78678862500

Electrical

Lamp Wattage - Maximum	75W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Voltage (Secondary) - Maximum	12V AC

Physical

Bulb Type	Incandescent
Cord Length - Primary	3.04m (10.0')
Cord Length - Secondary	7.62m (25.0')
Cord Type - Primary	16/3 SOOW
Cord Type - Secondary	14/2 SOOW
Depth	101.60mm (4.000")
Duty	Industrial
Guard Included	Yes
Guard Type	Screw Release
Height	374.65mm (14.750")
Lamp Type	A21
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton
