



Part Number : 1301100022
Product Description : Super-Safeway 500W Halogen Floodlight, Magnet Mount, with Guard, Cord Type 16/3 SOOW, Cord Length 7.62m (25.0')
Series Number : 130110
Status : Active
Product Category : Lamps and Lights
Engineering Number : 8506M



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights

Series	130110
Description	Super-Safeway 500W Halogen Floodlight, Magnet Mount, with Guard, Cord Type 16/3 SOOW, Cord Length 7.62m (25.0')
NEMA Configuration	NEMA 5-15
NEMA Rating	Rain Tight
Product Name	Super-Safeway
Type	Wide Area Lamps
UPC	78678885061

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	500W
Lumens	9200
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Quartz Halogen
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	N/A
Duty	Industrial
Guard Included	Yes
Guard Type	Steel
Height	374.65mm (14.750")
Lamp Type	T-3 RSC
Length	279.40mm (11.000")
Material - Globe	Tempered Glass
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Magnet
Outlet	None

Packaging Type	Carton
----------------	--------

This document was generated on Mar 26, 2025