



Part Number : 1301370180
Product Description : Super-Safeway Multiple Outlet Box, Extended Depth, 2-Sided, (1) NEMA 5-15 GFCI Receptacles with Flip Lid, Open Neutral Relay, Top-of-Box GCM, 0.91m 12/3 SOOW Cord on Both sides, 5-15 Plug & Conn
Series Number : 130137
Status : Active
Product Category : Power Distribution
Engineering Number : 3080-GFI



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power Distribution

Series	130137
Description	Super-Safeway Multiple Outlet Box, Extended Depth, 2-Sided, (1) NEMA 5-15 GFCI Receptacles with Flip Lid, Open Neutral Relay, Top-of-Box GCM, 0.91m 12/3 SOOW Cord on Both sides, 5-15 Plug & Conn
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	Multiple Outlet Box
UPC	78678875162

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	15.0A
GFCI	Yes
GFCI Reset	Manual
Ground Continuity Monitor	Yes
Open Neutral Relay	Yes
Voltage - Maximum	125V

Physical

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	1.83m (6.0')
Cord Type	12/3 SOOW
Feed-Thru	No
Flip Lid	No
Material - Housing	Rubber
Mounting Style	Portable
Number of Receptacles	1
Packaging Type	Carton
Receptacle Type	GFCI Duplex

This document was generated on Mar 26, 2025