



Part Number : 1301430252

Product Description : Super-Safeway Cordset,  
12 Gauge SOOW, 2 Pole/3 Wire, Cordset,  
Length 7.62m (25.0'), NEMA L5-30, 125V

Series Number : 130143

Status : Active

Product Category : Wiring Devices

Engineering Number : 2847A123



---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
--------	--------

Category	Wiring Devices
Series	130143
Description	Super-Safeway Cordset, 12 Gauge SOOW, 2 Pole/3 Wire, Cordset, Length 7.62m (25.0'), NEMA L5-30, 125V
IP Rating	N/A
NEMA Configuration	NEMA L5-30
Product Name	Super-Safeway
Specialty	N/A
Type	Cordset
UPC	78678870567

### Agency

CSA	LR6837
UL	E38085

### Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	125V

### Physical

Cord Type	12/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	7.62m (25.0')
Lighted Connector	No
Locking Blade	Yes
Net Weight	266.000/kg
Poles	2-pole/3-wire
Receptacle Type	Single