



Part Number : [1301430255](#)
Product Description : Super-Safeway Cordset,
12 Gauge SOOW, 2 Pole/3 Wire, Cordset,
Length 7.62m (25.0'), NEMA L6-30, 250V
Series Number : 130143
Status : Active
Product Category : Wiring Devices
Engineering Number : 2848A123



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices

Series	130143
Description	Super-Safeway Cordset, 12 Gauge SOOW, 2 Pole/3 Wire, Cordset, Length 7.62m (25.0'), NEMA L6-30, 250V
IP Rating	N/A
NEMA Configuration	NEMA L6-30
Product Name	Super-Safeway
Specialty	N/A
Type	Cordset
UPC	78678870579

Agency

CSA	LR6837
UL	E38085

Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Type	12/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	7.62m (25.0')
Lighted Connector	No
Locking Blade	Yes
Net Weight	136.000/kg
Poles	2-pole/3-wire
Receptacle Type	Single