



Part Number : [1301530126](#)
Product Description : Super-Safeway In-Line Industrial GFCI, IP69K, Portable, Single Phase, Manual Reset, NEMA 5-20 Watertite Plug and Receptacle, 20A, 120V, 0.61m (2.0') Cord Length
Series Number : 130153
Status : Active
Product Category : Power Distribution
Engineering Number : 20052-1M



Documents & Resources

Drawings
[1301530126_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Power Distribution
Series	130153
Description	Super-Safeway In-Line Industrial GFCI, IP69K, Portable, Single Phase, Manual Reset, NEMA 5-20 Watertite Plug and Receptacle, 20A, 120V, 0.61m (2.0') Cord Length
Enclosure Rating	NEMA 4X
NEMA Configuration	NEMA 5-20
Product Name	Super-Safeway
Type	GFCI Industrial Duty, Single Phase
UPC	78678889737

Agency

UL	E66308
----	--------

Electrical

Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	120V

Physical

Cord Diameter	10.67mm (.420")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')
Cord Type	12/3 SJEOOW
Feed-Thru	Yes
Flip Lid	No

Material - Housing	Nylon
Mounting Style	Portable
Net Weight	910.359/g
Number of Receptacles	1
Packaging Type	Bag
Receptacle Type	GFCI Single