



Part Number : [1300950138](#)
Product Description : Heavy Duty Wire Mesh
Pulling Grip, Double Weave, Rotating Eye,
Standard Mesh Length 0.914m (36.00"),
Approximate Break Strength 12337.71kg
(27200 lbs)
Series Number : 130095
Status : Active
Product Category : Cable Grips
Engineering Number : 35883



Documents & Resources

Drawings
[1300950138_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Cable Grips
Series	130095
Description	Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Standard Mesh Length 0.914m (36.00"), Approximate Break Strength 12337.71kg (27200 lbs)
Product Name	Heavy Duty
Type	Pulling Grip
UPC	78678835883

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	12337.71kg (27200 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	50.80-63.25mm (2.000-2.490")
Color - Grommet	N/A
Eye Diameter	1 5/8"
Eye Type	Rotating
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.914m (36.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A