



**Part Number :** [1300950150](#)  
**Product Description :** Light Duty Wire Mesh Pulling Grip, Single Weave, Flexible Rope Eye, Short Mesh Length 0.431m (1.41'), Approximate Break Strength 2630.84kg (5800 lbs)  
**Series Number :** 130095  
**Status :** Active  
**Product Category :** Cable Grips  
**Engineering Number :** 35905



## Documents & Resources

**Drawings**  
[1300950150\\_sd.pdf](#)

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	Cable Grips
Series	130095
Description	Light Duty Wire Mesh Pulling Grip, Single Weave, Flexible Rope Eye, Short Mesh Length 0.431m (1.41'), Approximate Break Strength 2630.84kg (5800 lbs)
Product Name	Light Duty
Type	Pulling Grip
UPC	78678835905

### Agency

CSA	LR32159
-----	---------

### Physical

Approximate Break Strength	2630.84kg (5800 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	31.75-37.85mm (1.250-1.490")
Color - Grommet	N/A
Eye Type	Flexible
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.431m (1.41')
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A