



**Part Number :** 1300950190

**Product Description :** Medium Duty Wire Mesh Pulling Grip, Single/Double Weave, Bale Eye, Long Mesh Length 1.219m (48.00"), Approximate Break Strength 8799.69kg (19400 lbs)

**Series Number :** 130095

**Status :** Active

**Product Category :** Cable Grips

**Engineering Number :** 35962



---

## Documents & Resources

### Drawings

1300950190\_sd.pdf

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Cable Grips
Series	130095
Description	Medium Duty Wire Mesh Pulling Grip, Single/Double Weave, Bale Eye, Long Mesh Length 1.219m (48.00"), Approximate Break Strength 8799.69kg (19400 lbs)
Product Name	Medium Duty
Type	Pulling Grip
UPC	78678835962

### Agency

CSA	LR32159
-----	---------

### Physical

Approximate Break Strength	8799.69kg (19400 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	38.10-50.55mm (1.500-1.990")
Color - Grommet	N/A
Eye Type	Flexible
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	1.219m (48.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A