



Part Number : [1300950225](#)

Product Description : Heavy Duty Wire Mesh
Slack Grip Cable, Closed Mesh, Double Weave,
Offset Eye, Medium Mesh Length 0.33m
(13.00") Approximate Break Strength
1360.78kg (3000 lbs)

Series Number : 130095

Status : Active

Product Category : Cable Grips

Engineering Number : 36101



Documents & Resources

Drawings

[1300950225_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Cable Grips
Series	130095
Description	Heavy Duty Wire Mesh Slack Grip Cable, Closed Mesh, Double Weave, Offset Eye, Medium Mesh Length 0.33m (13.00") Approximate Break Strength 1360.78kg (3000 lbs)
Product Name	Heavy Duty
Type	Pulling Grip
UPC	78678836101

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	1360.78kg (3000 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	19.05-25.15mm (.750-.990")
Color - Grommet	N/A
Eye Type	Offset
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.33m (13.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A