



Part Number : [1300950260](#)
Product Description : Medium Duty Wire Mesh Slack Grip Cable, Split Rod, Single Weave, Offset Eye, Medium Mesh Length 0.432m (17.00"), Approximate Break Strength 3492.66kg (7700 lbs)
Series Number : 130095
Status : Active
Product Category : Cable Grips
Engineering Number : 36146



Documents & Resources

Drawings
[1300950260_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Cable Grips
Series	130095
Description	Medium Duty Wire Mesh Slack Grip Cable, Split Rod, Single Weave, Offset Eye, Medium Mesh Length 0.432m (17.00"), Approximate Break Strength 3492.66kg (7700 lbs)
Product Name	Medium Duty
Type	Pulling Grip
UPC	78678836146

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	3492.66kg (7700 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	44.45-50.55mm (1.750-1.990")
Color - Grommet	N/A
Eye Type	Offset
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.432m (17.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A