



Part Number : 1301020284

Series Number : 130102

Product Category : Lamps and Lights

Product Description : Safeway Phenolic Hand Lamp, PAR 38 Guard, with Switch

Status : Active

Engineering Number : 282S

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130102
Description	Safeway Phenolic Hand Lamp, PAR 38 Guard, with Switch
NEMA Configuration	N/A
Product Name	Safety Yellow

Type	Hand Lamps
UPC	78678860701

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	240V

Physical

Bulb Type	Incandescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	190.50mm (7.500")
Duty	Commercial
Guard Included	Yes
Guard Type	Open End, PAR 38
Height	371.35mm (14.620")
Lamp Type	A21
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton