



Part Number : 1301050034
Product Description : Watertite Wet Location
30W 12V Spotlight with In-line Transformer,
Switch Screw Release Guard, 14/2 SOOW,
Overall Length 7.62m (50.0')
Series Number : 130105
Status : Active
Product Category : Lamps and Lights
Engineering Number : 1610S



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights

Series	130105
Description	Watertite Wet Location 30W 12V Spotlight with In-line Transformer, Switch Screw Release Guard, 14/2 SOOW, Overall Length 7.62m (50.0')
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Name	Watertite
Type	Hand Lamps, Specialty Light
UPC	78678861560

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	30W
Lumens	300
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ
Voltage (Secondary) - Maximum	12V AC

Physical

Bulb Type	Quartz Halogen
Cord Length - Primary	3.04m (10.0')
Cord Length - Secondary	15.24m (50.0')
Cord Type - Primary	16/3 SOOW
Cord Type - Secondary	14/2 SOOW
Depth	N/A
Duty	Wet Location
Guard Included	Yes
Guard Type	Screw Release
Height	127.00mm (5.000")
Lamp Type	PAR36
Length	228.60mm (9.000")
Material - Guard	#10 Gauge Vinyl Coated Steel
Mounting Style	Hand Held

Outlet	None
Packaging Type	Carton

This document was generated on Mar 26, 2025