

## SILVYN® KCLICK NPT

SILVYN® KCLICK NPT



Assembly time



Temperature-resistant



Variety of approval certifications

### Benefits

- Fast assembly
- Easy to disassemble
- High-tensile
- High sealing performance
- Can be rotated

### Application range

- In combination with protective conduit:
- SILVYN® RILL PA 6
- SILVYN® RILL PA 12
- Robot-building
- Rotating applications

### Norm references / Approvals

UL FILENUMBER E308201

### Product Make-up

- NPT connection thread
- Body with inner sealing
- Upper part with snap-in sleeve

Last Update (05.02.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**SILVYN® KCLICK NPT****Technical Data**

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC001176<br>ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose |
| Colour delivered:      | Black (RAL 9005), UV-resistant                                                                          |
| Material:              | PA6<br>Halogen-free                                                                                     |
| Protection rating:     | IP 68<br>IP 69                                                                                          |
| Temperature range:     | -40 °C to +115 °C                                                                                       |

**Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® KLICK NPT**

| Article number | Nominal size | Overall length mm | Thread length mm | Clear opening (mm) | For conduit with outer Ø (mm) | Suitable for SILVYN® RILL | Pieces / PU |
|----------------|--------------|-------------------|------------------|--------------------|-------------------------------|---------------------------|-------------|
| 61800705       | NPT 1/4"     | 34                | 11.5             | 7                  | 10.0                          | 10                        | 50          |
| 61800715       | NPT 3/8"     | 37                | 12               | 10                 | 13.0                          | 13                        | 50          |
| 61800725       | NPT 3/8"     | 39                | 12               | 12.5               | 15.8                          | 16                        | 50          |
| 61800745       | NPT 1/2"     | 43.5              | 13               | 17                 | 21.2                          | 21                        | 50          |
| 61800755       | NPT 3/4"     | 47.5              | 14               | 21                 | 28.5                          | 28                        | 25          |
| 61800765       | NPT 1"       | 52                | 16               | 27.5               | 34.5                          | 34                        | 25          |
| 61800775       | NPT 1 1/4"   | 77                | 18               | 36.5               | 42.5                          | 42                        | 25          |
| 61800784       | NPT 1 1/2"   | 89                | 18               | 42.5               | 54.5                          | 54                        | 10          |
| 61800785       | NPT 2"       | 92                | 21               | 48.5               | 54.5                          | 54                        | 10          |