



PIDG

TE Internal #: 323994
Butt Splice, 26 – 22 AWG, .12 – .24 mm² Wire, Serrated, .238 – .475 kcmil, 238 – 475 CMA, Copper, Yellow - Translucent, 8 Serration, PIDG

[View on TE.com >](#)

Terminals & Splices > Splices > PIDG Butt Splices



Splice Type: **Butt Splice**
Wire Size: **.12 – .24 mm²**
Sealable: **No**
Splice Features: **Serrated**

[All PIDG Butt Splices \(25\)](#)

Features

Product Type Features

Splice Accessory Type	Splice
Splice Type	Butt Splice
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Serrations	8
Compatible With Wire & Cable Type	Discrete Wire

Body Features

Product Weight	.411 g
Insulation Material	Copper, Nylon
Splice Features	Serrated
Primary Product Color	Yellow - Translucent



Contact Features

Military Part Class	Class I
Terminal Plating Material	Tin
Contact Base Material	Copper
Barrel Type	Closed

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	.238 – .475 kcmil
Compatible Insulation Diameter Range	2.08 mm[.082 in]
Terminal Material Thickness	.38 mm[.015 in]
Product Length	22.61 mm[.87 in]

Usage Conditions

Insulation Option	Fully Insulated
-------------------	-----------------

Industry Standards

Government Qualified Splice	Yes
-----------------------------	-----

Packaging Features

Packaging Quantity	50
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 59275
T-HEAD PIDG PG SH 26-20 ASSY



TE Part # 69344
PIDG 26-22 DIE SET




TE Part # 46121
DAHT PG PIDG 26-22 ASSY

Also in the Series | PIDG



Compression Connectors(17)



Crimp Wire Pins, Tabs & Ferrules(41)




Hand Crimping Tools(2)



Knife Disconnects(11)



Ring Terminals(588)



Spade Terminals(228)




Special Purpose Terminals(1)



Splices(41)


Customers Also Bought



TE Part #925367-4
MOD 4 REC.HSG 2X04P




TE Part #323975
SPLICE, BUTT, PIDG, 24-20




TE Part #244999-E
STVCD 128 F ABCD VVV 7-00 EE 5,5
* 247



TE Part #1-1616126-0
E311P=RELAY




TE Part #3-1617753-7
FCA-325-AY2




TE Part #60983-2
.058 PIN REC PTPPHBZ




TE Part #E86269-000
GELWRAP-33/10-200(B6)



TE Part #2-1616980-2
KALF512B2117C=CONTACTOR,3PST,
LATCHING,



TE Part #1616009-2
BP353A =OVERALL



TE Part #81587-000
VS-X1743

Documents

Product Drawings

SPLICE BUTT PIDG 26-24

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_323994_Y.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_323994_Y.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_323994_Y.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



[PIDG Terminals and Splices Quick Reference Guide](#)

English

[PIDG TERMINALS & SPLICES Quick Reference Guide](#)

English