



Home : Connectors : QMA : EZ-240-QM-X

EZ-240-QM-X

Type QMA, male (plug), straight, EZ style connector for LMR[®]-240 and TCOM[®]-240 type cables. The EZ-240-QM-X eliminates assembly errors and soldering with crimp-style outer contacts and spring finger inner contacts. It features a no-braid trim design, eliminating FOD and guaranteeing an optimal and consistent termination. The BeCu pins are designed to maximize surface contact and minimize current density. They provide a strong spring force making the EZ connectors a perfect choice for extreme cold and high- vibration applications

where the center conductor might contract. The QMA series offers a more convenient installation than SMA connectors, with a snap-on instead of a threaded coupling. Another benefit of eliminating the threaded coupling is the denser packaging since there is no requirement for wrench clearance.



Stock Code: **3190-6564**

QMA-male (plug)



Specs



Compatible
with



Hardware



CAD Model



Documentation



Ask an Expert

Specifications

Part Number	EZ-240-QM-X
Stock Code	3190-6564
Interface	QMA
Gender	Male (plug)
Orientation	Straight
PIM Rating	
Impedance (ohms)	50

Max Frequency (GHz)	6
VSWR Freq	<1.30:1
VSWR Frequency (GHz)	6
Coupling Nut	Knurl
Inner Contact Attach	Spring Finger
Outer Contact Attach	Crimp
Body Finish	Alballoy

Pin Finish	Gold
Length (mm)	30.5
Length (in)	1.2
Width (mm)	10.5
Width (in)	0.41
Weight (g)	12.99
Weight (lb)	0.03

Compatible with

LMR-240

LMR-240-MA

TCOM-240-FR

LMR-240-DB

LMR-240-PVC

LMR-240-FR

TCOM-240