



Home : Connectors : TNC : EZ-195-TM-X

## EZ-195-TM-X

Type TNC, male (plug), straight, EZ style connector for LMR<sup>®</sup>-195 type cables. The EZ-195-TM-X eliminates assembly errors and soldering with crimp-style outer contacts and spring finger inner contacts. It features a no-braid trim design, eliminating FOD and guaranteeing an optimal and consistent termination. The BeCu pins are designed to maximize surface contact and minimize current density. They provide a strong spring force making the EZ connectors a perfect choice for extreme cold and high- vibration applications

where the center conductor might contract. The TNC is a miniature, threaded, weatherproof connector with a contact design similar to a BNC series and a higher frequency performance.



Stock Code: **3190-6496**

TNC-male (plug)



Specs



Hardware



CAD Model



Documentation



Ask an Expert

Compatible  
with

## Specifications

Part Number	<b>EZ-195-TM-X</b>
Stock Code	<b>3190-6496</b>
Interface	<b>TNC</b>
Gender	<b>Male (plug)</b>
Orientation	<b>Straight</b>
PIM Rating	
Impedance (ohms)	<b>50</b>

Max Frequency (GHz)	<b>6</b>
VSWR Freq	<b>&lt;1.30:1</b>
VSWR Frequency (GHz)	<b>6</b>
Coupling Nut	<b>Hex/Knurl</b>
Inner Contact Attach	<b>Spring Finger</b>
Outer Contact Attach	<b>Crimp</b>
Body Finish	<b>Alballoy</b>

Pin Finish	<b>Gold</b>
Length (mm)	<b>30.7</b>
Length (in)	<b>1.21</b>
Width (mm)	<b>15.88</b>
Width (in)	<b>0.63</b>
Weight (g)	<b>19.82</b>
Weight (lb)	<b>0.04</b>

## Compatible with

LMR-195

LMR-195-DB

LMR-195-FR

## Tools and Accessories



CST-195



CCT-02



CCT-03