



Home : Connectors : TNC : EZ-400-TF-X

## EZ-400-TF-X

TNC female (jack), straight, EZ style connector for LMR<sup>®</sup>-400, TCOM<sup>®</sup>-400, and T-RAD<sup>®</sup>-400-FR cables. The EZ-400-TF-X eliminates assembly errors and soldering with crimp-style outer contacts and spring finger inner contacts. It features a no-braid trim design, eliminating FOD and guaranteeing an optimal and consistent termination. The BeCu pins are designed to maximize surface contact and minimize current density. They provide a strong spring force making the EZ connectors a perfect choice for extreme cold and high- vibration applications

where the center conductor might contract. The TNC is a miniature, threaded, weatherproof connector with a contact design similar to a BNC series and a higher frequency performance.



Stock Code: **3190-3049**

TNC-female (jack)



Specs



Hardware



CAD Model



Documentation



Ask an Expert

Compatible  
with

## Specifications

Part Number	<b>EZ-400-TF-X</b>
Stock Code	<b>3190-3049</b>
Interface	<b>TNC</b>
Gender	<b>Female (jack)</b>
Orientation	<b>Straight</b>
PIM Rating	<b>N/A</b>
Impedance (ohms)	<b>50</b>

Max Frequency (GHz)	<b>6</b>
VSWR Freq	<b>&lt;1.30:1</b>
VSWR Frequency (GHz)	<b>6</b>
Coupling Nut	<b>N/A</b>
Inner Contact Attach	<b>Spring Finger</b>
Outer Contact Attach	<b>Crimp</b>
Body Finish	<b>Alballoy</b>

Pin Finish	<b>Gold</b>
Length (mm)	<b>45</b>
Length (in)	<b>1.8</b>
Width (mm)	<b>14</b>
Width (in)	<b>0.55</b>
Weight (g)	<b>33.6</b>
Weight (lb)	<b>0.07</b>