



Home : Connectors : TNC : TC-240-TM-RA-D

TC-240-TM-RA-D

Type TNC, male (plug), right angle, TC style connector for FBT-240, LMR[®]-240, and TCOM[®]-240 type cables. The TC-240-TM-RA-D features a solder-pin connector and is a perfect option for stranded center conductors. The TNC is a miniature, threaded, weatherproof connector with a contact design similar to a BNC series and a higher frequency performance.



Stock Code: **3190-6547**

TNC-male (plug) right angle crimp connector,
solder-on pin



Specs



Compatible
with



Hardware



CAD Model



Documentation



Ask an Expert

Specifications

Part Number	TC-240-TM-RA-D
Stock Code	3190-6547
Interface	TNC
Gender	Male (plug)
Orientation	Right Angle
PIM Rating	
Impedance (ohms)	50

Max Frequency (GHz)	6
VSWR Freq	<1.35:1
VSWR Frequency (GHz)	6
Coupling Nut	Hex/Knurl
Inner Contact Attach	Solder
Outer Contact Attach	Crimp
Body Finish	Alballoy

Pin Finish	Gold
Length (mm)	33.3
Length (in)	1.31
Width (mm)	31.5
Width (in)	1.24
Weight (g)	32.44
Weight (lb)	0.07