



Home : Connectors : BNC : TC-240-BM-RA-D

TC-240-BM-RA-D

Type BNC, male (plug), right angle, TC style connector for FBT-240, LMR-240, and TCOM-240 type cables.



Stock Code: **3190-6552**

BNC-male (plug)



Specs



Compatible
with



Hardware



CAD Model



Documentation



Ask an Expert

Specifications

Part Number	TC-240-BM-RA-D
Stock Code	3190-6552
Interface	BNC
Gender	Male (plug)
Orientation	Right Angle
PIM Rating	
Impedance (ohms)	50

Max Frequency (GHz)	6
VSWR Freq	<1.35:1
VSWR Frequency (GHz)	6
Coupling Nut	Knurl
Inner Contact Attach	Solder
Outer Contact Attach	Crimp
Body Finish	Alballoy

Pin Finish	Gold
Length (mm)	29.7
Length (in)	1.17
Width (mm)	28.4
Width (in)	1.12
Weight (g)	25.09
Weight (lb)	0.06