

PSEN 1.1a-20/PSEN 1.1-20 /8mm/5m/1unit

504226



Magnetic safety switch 2 n/o, square design, height design 13 mm, IP6K9K, switching distance 8 mm, PU = 1 piece with actuator, with 5 m cable (PUR).

Technical details

General data

Approval:	CE, UKCA, cULus Listed, EAC (Eurasian), ECOLAB, TÜV
Sensor principle:	magnetic
Coding level to ISO 14119:	Low
Classification to EN 60947-5-3:	PDDb
Suitable for series connection:	no
unit type:	Unit

Technical data

Environment

RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	no
REACH compliance:	Contains no SVHC substances
WEEE classification (08/2018):	5 devices (feed size < 50cm)

Commercial data

ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27274401
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002544

UNSPSC 25:	39122205
GTIN:	4046548026627
Volume:	0 dm3
Harmonized System Code:	85365019
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1

Optional accessories



380308

PSS67 M12 connector, straight, male, 5pole



540310

PSEN screw M4x16 10pcs



380310

PSS67 M12 connector, angled, male, 5pole



532110

PSEN Winkel / bracket



534310

PSEN Distanzplatte / spacer (10 pcs.)



534320

PSEN reverse spacer (2 pcs.)