

PSEN cable axial M12 8-pole 30m

540326



Connection cable, PUR, yellow RAL1003, suitable for drag chains, 8-pin, socket straight M12, on open line end, A-coded, cable length: 30m

Technical details

General data	
Approval:	CE, UKCA, cULus Listed
Technical data	
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	6c
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1
SCIP entry available:	yes
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27060311
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001855

UNSPSC 25:	26121603
GTIN:	4046548025255
Volume:	0 dm3
Harmonized System Code:	85444290
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1