

MQDC2S-850

► SINGLE-ENDED CORDSETS



Cordset: Single Ended M12
8-pin Straight Female
16 m 8x24 Shielded Black PVC Jacket
Nickel-Plated Brass Coupling Nut
Part Number: 81538

CERTIFICATIONS



SPECIFICATIONS

Cordset Length (m)	16.00
Connector 1 Orientation	Straight
Outside Cable Diameter (mm)	5.70
Connector 1 Gender	Female
Trunk Length (m)	No Trunk
Cordset Length Range (m)	10.00-19.99
Cable Jacket Color	Black
Overmold Material and Color	PUR Black
Number of Ends	Single Ended

Connector 2 Type	Flying Leads
Connector 1 Type	M12
Connector 1 Number of Contacts	8
Coupling Nut Material	Nickel Plated Brass
Cable Jacket Material	PVC
IP Rating	IP67
Connector 1 Key Code	A
Shield/No Shield	Shield - Floating to Drain
Voltage Rating (V)	30 V ac/dc
Current Rating (A)	2.0
Minimum Temp. (Celsius)	-40
Maximum Temp. (Celsius)	70