

MQDC-WDSS-0430

► SINGLE-ENDED CORDSETS



Cordset: Single Ended M12
4-pin Straight Female
9 m (29.53 ft) 4x22 Black PVC Jacket
PVC Black; 316 Stainless Steel Coupling Nut
Part Number: 84918

CERTIFICATIONS



SPECIFICATIONS

Cordset Length (m)	9.00
Connector 1 Orientation	Straight
Outside Cable Diameter (mm)	4.80
Connector 1 Gender	Female
Trunk Length (m)	No Trunk
Cordset Length Range (m)	5.00-9.99
Cable Jacket Color	Black
Overmold Material and Color	PVC Black
Number of Ends	Single Ended

Connector 2 Type	Flying Leads
Connector 1 Type	M12
Connector 1 Number of Contacts	4
Coupling Nut Material	316 Stainless Steel
Cable Jacket Material	PVC
IP Rating	IP69
Connector 1 Key Code	A
Shield/No Shield	No Shield
Voltage Rating (V)	250 V ac/dc
Current Rating (A)	4
Minimum Temp. (Celsius)	-40
Maximum Temp. (Celsius)	70
Feature: Washdown Rated	Yes