


Brand	ASUS					
Company name	ASUSTeK COMPUTER INC.					
Contact information	greenasus@asus.com					
Internet site	http://www.asus.com					
Address	15, Li-Te Rd., Peitou, Taipei 112, Taiwan					
Issue date	29-Apr-20					
Product Type	AC-DC EPS		Manufacturer	Delta Electronics, Inc.		
Model Name	ADP-150CH B, D					
Input Voltage	100-240	V	Input AC Frequency	50-60	Hz	
Nameplate Output	20.0V - 7.5A , 150.0W		Energy Efficiency Level	Level VI		
Ecodesign Requirements	Information		Measured	Required	Result	
	Efficiency at low load 10%		83.49%	-	PASS	
	Average Active Efficiency		90.84%	88.0%	PASS	
	No-Load Power Consumption (W)		0.13	0.21	PASS	
Test voltage in V and frequency in Hz			230V, 50Hz			
Total harmonic distortion of the electricity supply system			<2%			
Nameplate Output: V(Voltage); A(Current); W(Power)						
The efficiency mark consists of a Roman numeral which printed on the external power supply nameplate, is accordance with International Efficiency Marking Protocol for External Power Supplies Version 3.0, September 2013.						
The instrumentation, set-up and circuits used for electrical testing are accordance with IEC 62301:2011 and EN50564:2011						