

PRODUCT CHANGE NOTIFICATION

Product Category PATHWAYS **20250224-1**

Product Group CONNECTIVITY & PATHWAYS

ISSUE DATE: ☒ 1/24 ☒ EMEA ☒ LATAM ☒ 18 Feb-25

IMPACTED REGIONS: ☒ DISCONTINUATION

REASON FOR CHANGE: ☐ OTHER

DESCRIPTION OF CHANGE: (Required)	
All FiberRunner 6-Foot and 2-Meter Channels and Covers will be discontinued and replaced by FiberRunner 10-Foot and 3-Meter Channels and Covers. The new 10-Foot and 3-Meter Channels and Covers are available now and will look and function the same as the 6-Foot and 2-Meter products they replace. The 10-Foot and 3-Meter Channels and Covers will reduce installation time and costs by allowing extended pathway lengths to be installed using fewer pathway lengths and end-to-end coupler connections. Production priority will be given to the new 10-Foot and 3-Meter lengths, and lead times may be longer for new orders of the 6-Foot and 2-Meter lengths until production ends and they are marked as "Use Up" on May 29, 2025. The Unit of Measure (UOM) for all new 10-Foot and 3-Meter Channels and Covers will be "Piece." FiberRunner will no longer use a unit of measure of Feet (for 6-foot) or Meter (for 2-Meter) for Channels and Covers.	



IMPACTED PART NUMBERS AND REPLACEMENT PART NUMBERS: (where applicable)

[Reference Page 2 / Linked PDF](#)

DATES: DISCONTINUATION AND NEW PRODUCT AVAILABILITY:

SCHEDULE FOR CHANGE	Year (YYYY)	Month (MM)	Day (DD)
New product sample availability date	2021	6	30
Old product discontinuation date*	2025	5	29

***Important:** A return material authorization (RMA) may be obtained for these affected part numbers and they may be returned up to 60 days after the product discontinuation announcement date if purchased within the last 18 months and subject to the return policy requirements outlined in Panduit's Authorized Distributor Policy. Please contact your local Panduit Customer Experience team if you have any questions.

CUSTOMER SERVICE CONTACTS

ASIA PACIFIC	AUSTRALIA: 1-800 7263848 AUS-CSVM@panduit.com	CHINA: 400-820-1900 CHN-CustomerService@panduit.com	HONG KONG: 800-965768 CHN-CustomerService@panduit.com
	INDIA: 000 800 6501844 (Fixed) 000 800 6500369 (Mobile) SGP-Customer_Service@panduit.com	INDONESIA: 001 803 65 7571 SGP-Customer_Service@panduit.com	JAPAN: +81-3-6863-6000 JPN-CS@panduit.com
	KOREA: 02-2182-7300 KOR-CustomerService@panduit.com	MALAYSIA 1800 801435 SGP-Customer_Service@panduit.com	SINGAPORE: 1-800-7263848 SGP-Customer_Service@panduit.com
	TAIWAN: 0080 165 1487 SGP-Customer_Service@panduit.com	THAILAND: 001-800-65-6385 SGP-Customer_Service@panduit.com	
LATIN AMERICA	BRAZIL 08000562613 (Toll Free) BRA-custservice@panduit.com	MEXICO: +52-33-37776000 x80520 01 800 360 86 00 (Toll Free) MEX-customer-service@panduit.com	OTHER LA COUNTRIES: Phone USA 1-708-532-1800 TP-CS-INTERNATIONAL@panduit.com

NORTH AMERICA	USA & CANADA: 1-800-777-3300 cs@panduit.com	EMEA	EMEA: +44 208 6017219 EMEA-CustomerServices@panduit.com
----------------------	--	-------------	--

IMPACTED PART NUMBER(s)	Replacement Part 1	IMPACTED PART NUMBER(s)	Replacement Part 1
FR12X4YL6	FR12X4YL10	FRHC4BL2	FRHC4BL3
FR12X4BL6	FR12X4BL10	FRHC6YL2	FRHC6YL3
FR4X4YL6	FR4X4YL10	FRHC6BL2	FRHC6BL3
FR4X4BL6	FR4X4BL10	FRSHC4YL2	FRSHC4YL3
FR6X4YL6	FR6X4YL10	FRSHC4BL2	FRSHC4BL3
FR6X4BL6	FR6X4BL10	FRSHC6YL2	FRSHC6YL3
FRHC12YL6	FRHC12YL10	FRSHC6BL2	FRSHC6BL3
FRHC12BL6	FRHC12BL10	HC2YL2	HC2YL3
FRHC4YL6	FRHC4YL10	HC2BL2	HC2BL3
FRHC4BL6	FRHC4BL10	HS2X2YL2	HS2X2YL3
FRHC6YL6	FRHC6YL10	HS2X2BL2	HS2X2BL3
FRHC6BL6	FRHC6BL10	HS2X2YL2NM	HS2X2YL3NM
FRSHC4YL6	FRSHC4YL10	HS2X2BL2NM	HS2X2BL3NM
FRSHC4BL6	FRSHC4BL10	FR12X4LYL2	FR12X4LYL3
FRSHC6YL6	FRSHC6YL10	FR12X4LBL2	FR12X4LBL3
FRSHC6BL6	FRSHC6BL10	FR4X4LYL2	FR4X4LYL3
HC2YL6	HC2YL10	FR4X4LBL2	FR4X4LBL3
HS2X2YL6NM	HS2X2YL10NM	FR6X4LYL2	FR6X4LYL3
HS2X2YL6	HS2X2YL10	FR6X4LBL2	FR6X4LBL3
HS2X2BL6NM	HS2X2BL10NM	FRHC12LYL2	FRHC12LYL3
HS2X2BL6	HS2X2BL10	FRHC12LBL2	FRHC12LBL3
FR12X4YL2	FR12X4YL3	FRHC4LYL2	FRHC4LYL3
FR12X4BL2	FR12X4BL3	FRHC4LBL2	FRHC4LBL3
FR4X4YL2	FR4X4YL3	FRHC6LYL2	FRHC6LYL3
FR4X4BL2	FR4X4BL3	FRHC6LBL2	FRHC6LBL3
FR6X4YL2	FR6X4YL3	FRSHC4LYL2	FRSHC4LYL3

FR6X4BL2	FR6X4BL3	FRSHC4LBL2	FRSHC4LBL3
FRHC12YL2	FRHC12YL3	FRSHC6LYL2	FRSHC6LYL3
FRHC12BL2	FRHC12BL3	FRSHC6LBL2	FRSHC6LBL3
FRHC4YL2	FRHC4YL3	HC2LYL2	HC2LYL3
HS2X2LBL2NM	HS2X2LBL3NM	HC2LBL2	HC2LBL3
		HS2X2LYL2NM	HS2X2LYL3NM